

**Table 293 - Section Hardware and Kits**

Description			Catalog Number	Price	Delivery Program	
End Closing Plate	Covers both top and bottom horizontal wireway openings and bus opening on one side of vertical section only. For use with sidesheets having internal c-channel mounting angle.	For 15" deep sections	NEMA Type 1 and Type 1 w/gasket	2100H-N3A1	\$165	SC
			NEMA Type 12	2100H-N3J1		
		For 20" deep sections	NEMA Type 1 and Type 1 w/gasket	2100H-N3A2	330	
			NEMA Type 12	2100H-N3J2		
Bottom Closing Plate	For 20" wide x 15" deep section		NEMA Type 1 or Type 1 w/gasket MCC (non-gasketed plates)	2100H-N1A1	105	
	For 20" wide x 20" deep section			2100H-N1A2		
	For 15" deep corner section			2100H-N1A1C	265	
	For 20" deep corner section			2100H-N1A2C		
External Mounting Channel Kits	Two (2) 1.5" x 3" mounting channels for a single section.		For 20" wide vertical section	2100H-NMC1	165	
	<b>NOTE:</b> Adding an external mounting channel will add 1.5" to height of section.		For 25" wide vertical section	2100H-NMC2	205	
			For 30" wide vertical section	2100H-NMC3	250	
			For 35" wide vertical section	2100H-NMC4	290	
			For 40" wide vertical section	2100H-NMC7	330	
			For 15" deep corner section	2100H-NMC5	510	
			For 20" deep corner section	2100H-NMC6	625	
Unit Operating Handle Extender			Permits unit operating handle to be located above the NEC 6' 7" handle-to-floor height limitation. Complies with NEC Article 404.8(A) and the UL Standard for Safety UL 845.		2100H-NE1	40
Space Heater Kit	200 watt, 120 volt strip heater with thermostat set at 21°C (70°F)		2100H-NH1	490		
	200 watt, 240 volt strip heater with thermostat set at 21°C (70°F)		2100H-NH2	770		
Gasketing Kit <sup>(1)</sup>	Gasketing to cover the section perimeter of two (2) 1.0 space factor doors or one (1) 1.5 through 5.0 space factor doors. For units mounted in series A through D sections.		2100H-GJ10	80		

(1) Cannot be air shipped.