

# Product Details and Certifications

**Product:** 22B-D010N104

**Description:** PowerFlex 40 AC Drive, 480VAC, 3PH, 10 Amps, 4 kW, 5 HP, Frame Size B, IP20 (Open), LED Display, Digital Keypad, No CE Compliant Filter, RS485



Representative Photo Only (actual product may vary based on configuration selections)

## ***BASE DRIVE INFORMATION***

---

Input Voltage	480VAC, 3PH
Output Current	10 Amps
Enclosure Style	IP20 (Open)
Frame Size	Frame Size B

## ***INSTALLED OPTIONS***

---

Human Interface Module (Type)	LED Display, Digital Keypad
Internal EMC Filtering	No CE Compliant Filter
Internal Communication Module	RS485

---

**Short Circuit Ratings Data Sheet for 22B-D010N104**

Operational Rating	Dual Element Time Delay Fuses			Non-Time Delay Fuses			Circuit Breakers							Rating Reference	File Ref: UL	File Ref: CSA	Comments
	SCCR [kA]	Max Fuse Size [A]	Fuse Class	SCCR [kA]	Max Fuse Size [A]	Fuse Class	CB Type	Catalog Number	SCCR [kA]	SCCR [kA]	SCCR [kA]	SCCR [kA]	SCCR [kA]				
	600V			600V					240V	480V	480Y/277V	600V	600Y/347V				
5 HP	200	20	CC, T, J	—	—	—	UL 508 Manual Motor Controller	140M-C2E-C16	—	30	—	30	—	User Guide	E59272	cUL	
—	—	—	—	—	—	—	UL 508 Type E Comb. Motor Controller	140M-C2E-C16	—	—	30	—	—	User Guide	E59272	cUL	
—	—	—	—	—	—	—	UL 489 MCCB	TBD	TBD	TBD	TBD	TBD	TBD	User Guide	E59272	cUL	
—	—	—	—	—	—	—	UL 489 MCP	TBD	TBD	TBD	TBD	TBD	TBD	User Guide	E59272	cUL	