

Product Details and Certifications

Product: 22B-D012N104

Description: PowerFlex 40 AC Drive, 480VAC, 3PH, 12 Amps, 5.5 kW, 7.5 HP, Frame Size C, IP20 (Open), LED Display, Digital Keypad, No CE Compliant Filter, RS485



Representative Photo Only (actual product may vary based on configuration selections)

BASE DRIVE INFORMATION

Input Voltage	480VAC, 3PH
Output Current	12 Amps
Enclosure Style	IP20 (Open)
Frame Size	Frame Size C

INSTALLED OPTIONS

Human Interface Module (Type)	LED Display, Digital Keypad
Internal EMC Filtering	No CE Compliant Filter
Internal Communication Module	RS485

Short Circuit Ratings Data Sheet for 22B-D012N104

Operational Rating	Dual Element Time Delay Fuses			Non-Time Delay Fuses			Circuit Breakers							Rating Reference	File Ref: UL	File Ref: CSA	Comments
	SCCR [kA]	Max Fuse Size [A]	Fuse Class	SCCR [kA]	Max Fuse Size [A]	Fuse Class	CB Type	Catalog Number	SCCR [kA]	SCCR [kA]	SCCR [kA]	SCCR [kA]	SCCR [kA]				
	600V			600V					240V	480V	480Y/277V	600V	600Y/347V				
7.5 HP	200	25	CC, T, J	—	—	—	UL 508 Manual Motor Controller	140M-D8E-C20	—	30	—	30	—	User Guide	E59272	cUL	
—	—	—	—	—	—	—	UL 508 Type E Comb. Motor Controller	140M-D8E-C20	—	—	30	—	—	User Guide	E59272	cUL	
—	—	—	—	—	—	—	UL 489 MCCB	TBD	TBD	TBD	TBD	TBD	TBD	User Guide	E59272	cUL	
—	—	—	—	—	—	—	UL 489 MCP	TBD	TBD	TBD	TBD	TBD	TBD	User Guide	E59272	cUL	