

Product Details and Certifications

Product: 22B-D2P3N104

Description: PowerFlex 40 AC Drive, 480VAC, 3PH, 2.3 Amps, 0.75 kW, 1 HP, Frame Size B, IP20 (Open), LED Display, Digital Keypad, No CE Compliant Filter, RS485



Representative Photo Only (actual product may vary based on configuration selections)

BASE DRIVE INFORMATION

| | |
|-----------------|--------------|
| Input Voltage | 480VAC, 3PH |
| Output Current | 2.3 Amps |
| Enclosure Style | IP20 (Open) |
| Frame Size | Frame Size B |

INSTALLED OPTIONS

| | |
|-------------------------------|-----------------------------|
| Human Interface Module (Type) | LED Display, Digital Keypad |
| Internal EMC Filtering | No CE Compliant Filter |
| Internal Communication Module | RS485 |

Short Circuit Ratings Data Sheet for 22B-D2P3N104

| Operational Rating | Dual Element Time Delay Fuses | | | Non-Time Delay Fuses | | | Circuit Breakers | | | | | | | Rating Reference | File Ref: UL | File Ref: CSA | Comments |
|--------------------|-------------------------------|-------------------|------------|----------------------|-------------------|------------|--------------------------------------|----------------|-----------|-----------|-----------|-----------|-----------|------------------|--------------|---------------|----------|
| | SCCR [kA] | Max Fuse Size [A] | Fuse Class | SCCR [kA] | Max Fuse Size [A] | Fuse Class | CB Type | Catalog Number | SCCR [kA] | SCCR [kA] | SCCR [kA] | SCCR [kA] | SCCR [kA] | | | | |
| | 600V | | | 600V | | | | | 240V | 480V | 480Y/277V | 600V | 600Y/347V | | | | |
| 1 HP | 200 | 6 | CC, T, J | — | — | — | UL 508 Manual Motor Controller | 140M-C2E-B40 | — | 65 | — | 25 | — | User Guide | E59272 | cUL | |
| — | — | — | — | — | — | — | UL 508 Type E Comb. Motor Controller | 140M-C2E-B40 | — | — | 65 | — | 25 | User Guide | E59272 | cUL | |
| — | — | — | — | — | — | — | UL 489 MCCB | TBD | TBD | TBD | TBD | TBD | TBD | User Guide | E59272 | cUL | |
| — | — | — | — | — | — | — | UL 489 MCP | TBD | TBD | TBD | TBD | TBD | TBD | User Guide | E59272 | cUL | |