

Product: 22D-D017N104

Description: PowerFlex 40P



Representati
Photo Only (actual product may va
based on configuration selections

BASE DRIVE INFORMATION

Input Voltage	480VAC, 3PH
Output Current	17 Amps
Enclosure Style	Panel Mount IP20 (NEMA Type Open)
Frame Size	Frame Size C

INSTALLED OPTIONS

Human Interface Module Version	Display w/ Reset Only
Filter Options	Without CE compliant filter
Internal Communication Module	Standard