

Product: 22D-D024N104

Description: PowerFlex 40P



Representati
Photo Only (actual product may va
based on configuration selections

BASE DRIVE INFORMATION

| | |
|-----------------|-----------------------------------|
| Input Voltage | 480VAC, 3PH |
| Output Current | 24 Amps |
| Enclosure Style | Panel Mount IP20 (NEMA Type Open) |
| Frame Size | Frame Size C |

INSTALLED OPTIONS

| | |
|--------------------------------|-----------------------------|
| Human Interface Module Version | Display w/ Reset Only |
| Filter Options | Without CE compliant filter |
| Internal Communication Module | Standard |