

**Product:** 22D-D6P0N104

**Description:** PowerFlex 40P



Representati  
Photo Only (actual product may va  
based on configuration selections

**BASE DRIVE INFORMATION**

Input Voltage	480VAC, 3PH
Output Current	6 Amps
Enclosure Style	Panel Mount IP20 (NEMA Type Open)
Frame Size	Frame Size B

**INSTALLED OPTIONS**

Human Interface Module Version	Display w/ Reset Only
Filter Options	Without CE compliant filter
Internal Communication Module	Standard