

➔ Cross Reference RA Part Number: **PN-620524**

➔ Product: **25-RF011-AL**



EMC Filters (Required to Meet CE Certification)

Drive Ratings Input Voltage					Frame	Cat. No.	Used with PowerFlex Drive		
	Normal Duty		Heavy Duty				PF523	PF525	PF527
➔ 100...120V, Single-Phase, 50/60 Hz	0.2	0.25	0.2	0.25	A	25-RF011-AL	✓		
	0.4	0.5	0.4	0.5	A		✓	✓	✓
	0.75	1	0.75	1	B	25-RF023-BL	✓	✓	✓
	1	1.5	1	1.5	B		✓	✓	✓
200...240V, Single-Phase, 50/60 Hz	0.2	0.25	0.2	0.25	A	25-RF011-AL	✓		
	0.4	0.5	0.4	0.5	A		✓	✓	✓
	0.75	1	0.75	1	A		✓	✓	✓
	1.5	2	1.5	2	B	25-RF023-BL	✓	✓	✓
	2.2	3	2.2	3	B		✓	✓	✓
200...240V, Three-Phase 50/60 Hz,	0.2	0.25	0.2	0.25	A	25-RF014-AL	✓		
	0.4	0.5	0.4	0.5	A		✓	✓	✓
	0.75	1	0.75	1	A		✓	✓	✓
	1.5	2	1.5	2	A		✓	✓	✓
	2.2	3	2.2	3	A		✓	✓	✓
	3.7	5	3.7	5	B	25-RF021-BL	✓	✓	✓
	5.5	7.5	5.5	7.5	C	25-RF027-CL	✓	✓	✓
	7.5	10	7.5	10	D	25-RF035-DL	✓	✓	✓
	11	15	11	15	E	25-RF056-EL	✓	✓	✓
	15	20	11	15	E		✓	✓	✓
380...480V, Three-Phase 50/60 Hz	0.4	0.5	0.4	0.5	A	25-RF7P5-AL	✓	✓	✓
	0.75	1	0.75	1	A		✓	✓	✓
	1.5	2	1.5	2	A		✓	✓	✓
	2.2	3	2.2	3	A		✓	✓	✓
	3.7	5	3.7	5	B	25-RF014-BL	✓	✓	✓
	5.5	7.5	5.5	7.5	C	25-RF018-CL	✓	✓	✓
	7.5	10	7.5	10	C		✓	✓	✓
	11	15	11	15	D	25-RF033-DL	✓	✓	✓
	15	18.5	11	15	D		✓	✓	✓
	18.5	22	15	20	E	25-RF039-EL	✓	✓	✓
	22	30	18.5	25	E		✓	✓	✓
	525...600V, Three-Phase, 50/60 Hz	0.4	0.5	0.4	0.5	A	25-RF8P0-BL	✓	✓
0.75		1	0.75	1	A		✓	✓	✓
1.5		2	1.5	2	A		✓	✓	✓
2.2		3	2.2	3	A		✓	✓	✓
3.7		5	3.7	5	B		✓	✓	✓
5.5		7.5	5.5	7.5	C	25-RF014-CL	✓	✓	✓
7.5		10	7.5	10	C		✓	✓	✓
11		15	11	15	D	25-RF027-DL	✓	✓	✓
15		18.5	11	15	D		✓	✓	✓
18.5		22	15	20	E	25-RF029-EL	✓	✓	✓
22		30	18.5	25	E		✓	✓	✓