

Bulletin 2193M 3-Pole Main Circuit Breaker (MCB), continued

Frame		Range of Available Trips (Amperes)	Interrupting Capacity Ratings (rms symmetrical Amperes)			Space Factor ⁽²⁾
Rating (Amperes)	Type		208V/240V	380V/400V 415V/480V	600V	
800	MDL	400...800	65k	50k	25k	2.5
	MDLG		65k	50k	25k	
	HMDL		100k	65k	35k	
	HMDLG		100k	65k	35k	
	NDC		100k	100k	65k	
	NDCG		100k	100k	65k	
	MDL HI-MAG	800	42k	35k	22k	
1200	ND	600...1200	65k	50k	25k	3.5
	NDG		65k	50k	25k	
	HND		100k	65k	35k	
	HNDG		100k	65k	35k	
	NDC		100k	100k	65k	
	NDCG		100k	100k	65k	
	ND HI-MAG	1200	65k	50k	25k	
2000 ⁽¹⁾	RD	1200...2000	100k	65k	50k	6.0, 30" W, 20" D
	RDG		100k	65k	50k	

(1) These units only can be used on systems of 65kA available or less. If 100kA is required, contact your local authorized Allen-Bradley distributor or Rockwell Automation Sales Office.

(2) Adding options may increase the space factor of the unit.