

# 2.3

## Molded Case Circuit Breakers

Series C

### CROSS TO ROCKWELL PART NUMBER 25107-455-07

Type NDC Electronic Circuit Breakers with Non-Interchangeable Trip Units

Order as individual components: breaker frame, rating plug, terminals.

2

#### Type NDC Electronic Circuit Breakers with Non-Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40°C	Digitrip RMS 310 Circuit Breaker Frame Only				Digitrip RMS 310 Rating Plug Only		Adjustable Rating Plug	Standard Terminals Only ①
	Ultra High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac							
	Standard	Options			Ampere Rating	Fixed Rating Plugs Catalog Number	Adjustable Ampere Ratings	See Page V4-T2-252 for Optional Terminals
Adjustable Short Time Pickup with I <sup>2</sup> t Short Delay Ramp Catalog Number	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I <sup>2</sup> t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Delay and Ground Fault Protection					
<b>Two-Pole</b>								
800	NDC2800T33W	NDC2800T32W	NDC2800T35W	NDC2800T36W	400	8NES400T	Adjustable settings are: 400, 500, 600, 800 <b>A8NES800T1</b>	TA700NB1
					450	8NES450T		TA700NB
					500	8NES500T		TA700NB1
					600	8NES600T		TA700NB1
					700	8NES700T		TA700NB1
					800	8NES800T		TA1000NB1
1200	NDC212T33W	NDC212T32W	NDC212T35W	NDC212T36W	600	12NES600T	Adjustable settings are: 600, 800, 1000, 1200 <b>A12NES1200T1</b>	TA700NB1
					700	12NES700T		TA700NB1
					800	12NES800T		TA1000NB1
					900	12NES900T		TA1000NB
					1000	12NES1000T		TA1000NB1
					1200	12NES1200T		TA1200NB1
<b>Three-Pole</b>								
800	NDC3800T33W	NDC3800T32W	NDC3800T35W	NDC3800T36W	400	8NES400T	Adjustable settings are: 400, 500, 600, 800 <b>A8NES800T1</b>	TA700NB1
					450	8NES450T		TA700NB1
					500	8NES500T		TA700NB1
					600	8NES600T		TA700NB1
					700	8NES700T		TA700NB1
					800	8NES800T		TA1000NB1
1200	NDC312T33W	NDC312T32W	NDC312T35W	NDC312T36W	600	12NES600T	Adjustable settings are: 600, 800, 1000, 1200 <b>A12NES1200T1</b>	TA700NB1
					700	12NES700T		TA700NB1
					800	12NES800T		TA1000NB
					900	12NES900T		TA1000NB1
					1000	12NES1000T		TA1000NB1
					1200	12NES1200T		TA1200NB1



**Note**  
① Two terminals are required per pole.