

**ALLEN-BRADLEY TO CUTLER-HAMMER (Westinghouse) BREAKER
CROSS-REFERENCE**

ALLEN-BRADLEY PART NUMBER	CUTLER-HAMMER CATALOG NUMBER	CONTINUOUS AMP RATING	INSTANTANEOUS TRIP SET	
			LOW	HI
'HMCP' 600 AMP FRAME MOTOR CIRCUIT PROTECTOR ("L" FRAME)				
25103-412-01	HMCP600L5W	600	3000	6000

SELTRONIC 600A "LD" FRAME BREAKER W/DIGITRIP 310 TRIP				
ALLEN-BRADLEY PART NUMBER	CUTLER-HAMMER CATALOG NUMBER	CONTINUOUS AMP RATING	MINIMUM TRIP RATING	NOTES
25103-406-01	LDB3600FT33W	600	300	STANDARD FRAME
25103-406-02	HLDB3600FT33	600	300	HI-INTERRUPTING
25103-406-03	LD3600KW	600	*	HI-MAG MOLDED CASE SWITCH
25103-406-04	LDCB3600FT33W	600	*	CURRENT LIMITING SWITCH
25103-407-01	LDB3600FT35W	600	300	LD WITH GROUND FAULT
25103-407-02	HLDB3600FT35W	600	300	HLD WITH GROUND FAULT
25103-407-03	LDCB3600FT35W	600	*	CURRENT LIMITING SWITCH

RATING PLUG FOR "LD" FRAME BREAKER (ONE REQUIRED PER BREAKER)				
ALLEN-BRADLEY PART NUMBER	CUTLER-HAMMER CATALOG NUMBER	CONTINUOUS AMP RATING	INSTANTANEOUS TRIP SET	
			LOW	HI
25107-447-01	6LES300T	300	600	2400
25107-447-02	6LES350T	350	700	2800
25107-447-03	6LES400T	400	800	3200
25107-447-04	6LES500T	500	1000	4000
25107-447-05	6LES600T	600	1200	4800

* NO RATING PLUG REQUIRED ON MOLDED CASE SWITCHES

SELTRONIC 800 A "MD" FRAME SOLID STATE THERMAL MAGNETIC BREAKER				
ALLEN-BRADLEY PART NUMBER	CUTLER-HAMMER CATALOG NUMBER	CONTINUOUS AMP RATING	MINIMUM TRIP RATING	NOTES
25103-458-01	MDS3800F	800	400	STANDARD FRAME
25103-458-02	MD3800WK	800	*	HI-MAG MOLDED CASE SWITCH
25103-459-01	MDSG3800F	800	400	MC WITH GROUND FAULT

RATING PLUG FOR "MC/MD" FRAME BREAKER (ONE REQUIRED PER BREAKER)				
ALLEN-BRADLEY PART NUMBER	CUTLER-HAMMER CATALOG NUMBER	CONTINUOUS AMP RATING	INSTANTANEOUS TRIP SET	
			LOW	HI
25107-450-01	8MC400	400	1200	4000
25107-450-02	8MC500	500	1500	5000
25107-450-03	8MC600	600	1800	6000
25107-450-04	8MC700	700	2100	7000
25107-450-05	8MC800	800	2400	8000

* NO RATING PLUG REQUIRED ON MOLDED CASE SWITCHES