



ALL DIMENSIONS
REFERENCE ONLY

CROSS REF
FOR
25107-504-04



1.0 DESCRIPTION: FIXED RATING PLUG FOR 1200 AMP WESTINGHOUSE N-FRAME
CIRCUIT BREAKER (SOLID STATE TRIP)

2.0 REQUIREMENTS

2.1 RATINGS: SEE TABLE BELOW

2.2 FOR USE WITH A-B PART NUMBER 25103-506 (CIRCUIT BREAKER)

3.0 QUALITY ASSURANCE AT A-B: VISUAL ONLY

4.0 VENDOR MODIFICATION: A-B MUST BE NOTIFIED OF ANY CHANGES IN MATERIALS OR
PROCESSES WHICH COULD AFFECT THE PERFORMANCE, RELIABILITY OR PHYSICAL
CHARACTERISTICS OF THIS DEVICE.

5.0 PACKAGING:

SHIPPING CONTAINERS MUST BE MARKED WITH MANUFACTURER'S NAME AND
PART NUMBER.

PART NO.	CHG. LTR.	RATING (AMPS)	FIXED PLUG RESISTANCE (k OHMS)		REFERENCE WESTINGHOUSE P/N
			MIN.	MAX.	
-01	A	600	36.1	36.9	12NES600T
-02	A	700	29.8	30.4	12NES700T
-03	A	800	24.6	25.1	12NES800T
-04	A	900	21.3	21.7	12NES900T
-05	A	1000	18.0	18.4	12NES1000T
-06	A	1200	13.5	13.8	12NES1200T

REFERENCE

**FIXED RATING PLUG
FOR 1200A N-FRAME
CIRCUIT BREAKER**

THIS DRAWING IS THE PROPERTY OF
THE ALLEN-BRADLEY CO. INC.
AND MAY NOT BE COPIED, USED OR
DISCLOSED FOR ANY PURPOSE EXCEPT
AS AUTHORIZED IN WRITING BY
THE ALLEN-BRADLEY CO. INC.



LOCATION: MILWAUKEE, WISCONSIN U.S.A.

DIMENSIONS APPLY BEFORE
SURFACE TREATMENT

(DIMENSIONS IN INCHES)
TOLERANCES UNLESS
OTHERWISE SPECIFIED

.XX: ± .02

.XXX: ± .005

ANGLES: ± 1°

DR. E. BROSS	DATE 12/13/01
CHKD. <i>E. Bross</i>	DATE 12-13-01
APPD. <i>G. Bruski</i>	DATE 12-14-01

DWG.
SIZE

A

SHEET 1 OF 1

25107-504