

Product Details and Certifications

Product: 25111-034-10
Description: Lighting Panel 3PH 4W 277/480 VAC MAX,
225AMP MLO Cu/Tin 18CKT



Representative Photo Only (actual product may vary based on configuration selections)

Data

Number of 1 pole circuits available	18
Panel Bus Material	Cu/Tin
Eaton Style Ref. Number	PRL2a
Branch Circuit Breakers	Bolt-on

Certifications and Approvals

UL	Panel boards: UL 67 Cabinets and boxes: UL 50
NEMA	PB 1
Federal Specification W-P-115c:	Circuit Breakers – Type I Class I Fusible Switch – Type II Class I