

ELECTRONIC/GLASS FUSES



GGC / GGC-V


Glass Body
Fast Acting
1/4" x 1-1/4"
1-1/2" Axial Leads Optional

1/100A through 10A, 250VAC, UL Listed and CSA Certified
12A and 15A, 125VAC, UL Listed and CSA Certified
20A through 30A, 32VAC

Standard Fuse Ampere Ratings

CATALOG NUMBER	AXIAL LEAD CAT. NO	AMPERE RATING	VOLTS	I.R.
GGC1/100	GGC-V1/100	1/100A	250V	1
GGC1/32	GGC-V1/32	1/32A	250V	1
GGC1/16	GGC-V1/16	1/16A	250V	1
GGC1/10	GGC-V1/10	1/10A	250V	2
GGC1/8	GGC-V1/8	1/8A	250V	2
GGC15/100	GGC-V15/100	15/100A	250V	2
GGC175/1000	GGC-V175/1000	175/1000A	250V	2
GGC3/16	GGC-V3/16	3/16A	250V	2
GGC2/10	GGC-V2/10	2/10A	250V	2
GGC1/4	GGC-V1/4	1/4A	250V	2
GGC3/10	GGC-V3/10	3/10A	250V	2
GGC3/8	GGC-V3/8	3/8A	250V	2
GGC4/10	GGC-V4/10	4/10A	250V	2
GGC1/2	GGC-V1/2	1/2A	250V	2
GGC6/10	GGC-V6/10	6/10A	250V	2
GGC3/4	GGC-V3/4	3/4A	250V	2
GGC8/10	GGC-V8/10	8/10A	250V	2
GGC1	GGC-V1	1A	250V	2
GGC1-1/4	GGC-V1-1/4	1-1/4A	250V	2
GGC1-1/2	GGC-V1-1/2	1-1/2A	250V	2
GGC1-3/4	GGC-V1-3/4	1-3/4A	250V	2
GGC1-6/10	GGC-V1-6/10	1-6/10A	250V	2
GGC2	GGC-V2	2A	250V	2
GGC2-1/4	GGC-V2-1/4	2-1/4A	250V	2
GGC2-1/2	GGC-V2-1/2	2-1/2A	250V	2
GGC3	GGC-V3	3A	250V	2
GGC3-2/10	GGC-V3-2/10	3-2/10A	250V	3
GGC4	GGC-V4	4A	250V	2
GGC5	GGC-V5	5A	250V	2
GGC6	GGC-V6	6A	250V	2
GGC6-3/10	GGC-V6-3/10	6-3/10A	250V	2
GGC7	GGC-V7	7A	250V	2
GGC7-1/2	N/A	7-1/2A	250V	2
GGC8	GGC-V8	8A	250V	2
GGC10	GGC-V10	10A	250V	2
GGC12	GGC-V12	12A	125V	4
GGC15	GGC-V15	15A	125V	4
GGC20	GGC-V20	20A	32V	5
GGC25	GGC-V25	25A	32V	5
GGC30	GGC-V30	30A	32V	5

- 250VAC @ 35A I.R./125VAC @ 10kA I.R.
- 250VAC @ 200A I.R./125VAC @ 10kA I.R.
- 250VAC @ 10kA I.R.
- 125VAC @ 10kA I.R.
- 32VAC @ 1000A I.R.



GGM / GGM-V

Glass Body
Fast Acting
5mm x 20mm
1-1/2" Axial Leads Optional

1/16A through 3A, 250VAC, UL Listed and CSA Certified
4A through 8A, 125VAC, UL Listed and CSA Certified
10A and 15A, 250VAC, UL Recognized

Standard Fuse Ampere Ratings

CATALOG NUMBER	AXIAL LEAD CAT. NO	AMPERE RATING	VOLTS	I.R.
GGM1/16	GGM-V1/16	1/16A	250V	2
GGM1/10	GGM-V1/10	1/10A	250V	3
GGM1/8	GGM-V1/8	1/8A	250V	3
GGM2/10	GGM-V2/10	2/10A	250V	3
GGM1/4	GGM-V1/4	1/4A	250V	3
GGM3/10	GGM-V3/10	3/10A	250V	3
GGM4/10	GGM-V4/10	4/10A	250V	1
GGM1/2	GGM-V1/2	1/2A	250V	3
GGM6/10	GGM-V6/10	6/10A	250V	1
GGM7/10	GGM-V7/10	7/10A	250V	3
GGM3/4	GGM-V3/4	3/4A	250V	3
GGM8/10	GGM-V8/10	8/10A	250V	1
GGM1	GGM-V1	1A	250V	3
GGM1-2/10	N/A	1-2/10A	250V	2
GGM1-1/4	GGM-V1-1/4	1-1/4A	250V	3
GGM1-1/2	GGM-V1-1/2	1-1/2A	250V	3
GGM1-6/10	GGM-V1-6/10	1-6/10A	250V	2
GGM2	GGM-V2	2A	250V	3
GGM2-1/2	GGM-V2-1/2	2-1/2A	250V	3
GGM3	GGM-V3	3A	250V	3
GGM4	GGM-V4	4A	125V	4
GGM5	GGM-V5	5A	125V	4
GGM6	GGM-V6	6A	125V	4
GGM7	GGM-V7	7A	125V	4
GGM8	GGM-V8	8A	125V	4
GGM10	GGM-V10	10A	250V	5
GGM15	GGM-V15	15A	250V	5

- 250VAC @ 35A I.R./125VAC @ 10kA I.R.
- 250VAC @ 100A I.R./125VAC @ 10kA I.R.
- 250VAC @ 200A I.R./125VAC @ 10kA I.R.
- 125VAC @ 10kA I.R.
- 250VAC @ 100A I.R.