

CROSS REF  
FOR  
25184-257-44



Littelfuse  
UL Class J Fuses, JTD\_ID Series

ITEM # JTD250ID

MFG # JTD250ID

Series JTD\_ID

Fuse, 250 Amps, 600 VAC

[More ...]

ORDER TODAY: *Est. Lead Time 10 days*  
or

FOR OTHER DELIVERY OPTIONS:

Unit Price: \$ 197.62

QTY.

#### Specifications for Littelfuse JTD250ID

Item Number:	JTD250ID
Manufacturer:	Littelfuse
Item Category:	Fuses
Subcategory:	UL Class J
Series:	JTD_ID
Amps:	250
Volts AC:	600
Volts DC:	500
Characteristic:	Time Delay
Package Type:	Center Bladed
Interrupt Rating:	300KA @ 600V
Trip Indicator:	Yes
Alarm Contact:	No
RoHS:	No
Approvals:	UL; CSA
Length (mm):	181 Millimeters
Diam. (mm):	50.8 Millimeters
Body Length (mm):	85.7 Millimeters
Mounting Centers (mm):	130.2; 136.5 Millimeters
Diam. (in.):	2 Inches
Length (in.):	7.13 Inches
Body Length (in.):	3.38 Inches
Mounting Centers:	5.13; 5.38 Inches
Picture No.:	LF_FUSE_ULJ_JTD_ID_225-400A