

CROSS REF  
FOR  
25184-257-47



**Littelfuse**  
**UL Class J Fuses, JTD\_ID Series**

ITEM # JTD400ID

MFG # JTD400ID

Series JTD\_ID

Fuse, 400 Amps, 600 VAC

[More ...]

O r

FOR —

U.62

QTY.

**Specifications for Littelfuse JTD400ID Item Number:** JTD400ID

**Manufacturer:** Littelfuse  
**Item Category:** Fuses  
**Subcategory:** UL Class J  
**Series:** JTD\_ID  
**Amps:** 400  
**Volts AC:** 600  
**Volts DC:** 500  
**Characteristic:** Time Delay  
**Package Type:** Center Bladed  
**Interrupt Rating:** 300KA @ 600V  
**Trip Indicator:** Yes  
**Alarm Contact:** No  
**RoHS:** No  
**Approvals:** UL; CSA  
**Length (mm):** 181 Millimeters  
**Diam. (mm):** 50.8 Millimeters  
**Body Length (mm):** 85.7 Millimeters  
**Mounting Centers (mm):** 130.2; 136.5 Millimeters  
**Diam. (in.):** 2 Inches  
**Length (in.):** 7.13 Inches  
**Body Length (in.):** 3.38 Inches  
**Mounting Centers:** 5.13; 5.38 Inches  
**Picture No.:** LF\_FUSE\_ULJ\_JTD\_ID\_225-400A