

CURRENT TRANSFORMERS

Model 7
Window Diameter 2.50"

APPLICATION:
With ammeters, wattmeters, and
cross current compensation.
FREQUENCY:
50-400 Hz.
INSULATION LEVEL:
600 Volts, 10 kV BIL full wave.

- Flexible leads are UL 1015 105 °C, CSA approved, #16 AWG, 24" long.
- Non-standard length to be specified.
- Terminals are brass studs No. 8-32 UNC with one flat washer, lockwasher and regular nut.
- SFT and SHT case styles also available as SFL and SHL with leads.
- Mounting bracket kit 0221B00182 when required for Model 7SHT.
- Approximate weight: 1.5 lb.

