

## Product Details and Certifications

**Product:** 40126-947-09

**Description:** 70A Molded Case Circuit Breaker, 3-Pole, Frame Size I, Medium Breaking Capacity, with (1) 1a-1b left-side

### SYSTEM VOLTAGE DATA

Supply Voltage, Maximum	600V 60Hz
Maximum Available Fault Current	100kA@240V, 65kA@480V, 25kA@600V

### CIRCUIT BREAKER

Circuit Breaker Type	Molded Case Circuit Breaker
Application	Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Fixed Magnetic)
Rated Operational Current (A)	70A
Frame Size	Frame Size I
Magnetic Trip Current (A)	600A Min - 1200A Max Fixed
Breaking Capacity	Medium Breaking Capacity
Certifications	UL 489, CSA 22.2 No. 5

### FACTORY OPTIONS

Factory Modifications - Left Front Mounting	1NO/1NC (1a-1b) auxiliary contact
Factory Modifications - Right Front Mounting	None

### TERMINAL LUG DATA

Important Information!	#14AWG - #1/0 AWG, Cu/Al
------------------------	--------------------------

### Dimensions and Weight

Weight (kg / lbs)	2.04 / 4.5
-------------------	------------