

Product Details

Product: 505V-EOH

Description: NEMA Full Voltage Reversing Starter, SIZE 4, with Eutectic Alloy Overload Relay

SYSTEM VOLTAGE DATA

Supply Voltage	208V 60Hz
Phases	3 Phase

STARTER DATA

Horsepower	40 HP
NEMA Size	NEMA 4
Enclosure Type	Open
Vertically Arranged Starter	Yes
Coil Voltage	200-208V 60Hz

OPTIONS

Overload Relay	Eutectic Alloy
Solenoid Option	No

Certifications and Approvals

NEMA/EEMAC	ICS 2 (Industrial Controls and Systems)
UL	508
CSA	22.2, No. 14
ABS	4/5.115
USCG	46 CFR 111.70
IEEE	45
UL	Listed (File No. E3125; Guide No. NLDX, NLDX2, NPKR)
CSA	Certified (LR 1234)
CE	Marked (Per EN 60947)
ABS	American Bureau of shipping

Recommended Spare Parts

CE-249	2	COIL,200/208V 60HZ FOR STARTER OR CONTACTOR
--------	---	---