

## Product Details and Certifications

**Product:** 505V-FOB-23

**Description:** 505 NEMA Full Voltage Reversing Starter

### SYSTEM VOLTAGE DATA

|                |           |
|----------------|-----------|
| Supply Voltage | 480V 60Hz |
| Phases         | 3 Phase   |

### STARTER DATA

|                             |               |
|-----------------------------|---------------|
| Horsepower                  | 200 HP        |
| NEMA Size                   | NEMA 5        |
| Enclosure Type              | Open          |
| Vertically Arranged Starter | Yes           |
| Coil Voltage                | 460-480V 60Hz |

### OPTIONS

|                |                        |
|----------------|------------------------|
| Overload Relay | No Overload Protection |
|----------------|------------------------|

### IMPORTANT INFORMATION

|   |                      |
|---|----------------------|
| Enclosure Size [length x width x depth] | Open Style / Unknown |
|---|----------------------|

### CERTIFICATIONS AND APPROVALS

|                                  |   |
|----------------------------------|---|
| NEMA/EEMAC                       | ICS 2 (Industrial Controls and Systems)   |
| UL                               | 508   |
| CSA                              | 22.2, No. 14  |
| ABS                              | 4/5.115   |
| USCG                             | 46 CFR 111.70   |
| IEEE                             | 45  |
| UL                               | Listed (File No. E3125; Guide No. NLDX, NLDX2, NPKR)  |
| CSA                              | Certified (LR 1234)   |
| CE                               | Marked (Per EN 60947)   |
| ABS                              | American Bureau of shipping   |
| For UL Certifications Directory: | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> |