

Product: 505V-FOD
Description: 505 NEMA Full Voltage Reversing Starter



Representat
 Photo Only (actual product may vary base
 on configuration selections)

SYSTEM VOLTAGE DATA

Phases 3 Phase

STARTER DATA

NEMA Size NEMA 5

Enclosure Type Open

Vertically Arranged Starter Yes

Coil Voltage 115-120V 60Hz

OPTIONS

Overload Relay Eutectic Alloy

IMPORTANT INFORMATION

Enclosure Size [length x width x depth] Open Style / Unknown

CERTIFICATIONS AND APPROVALS

NEMA/EEMAC ICS 2 (Industrial Controls and Systems)

UL 508

CSA 22.2, No. 14

ABS 4/5.115

USCG 46 CFR 111.70

IEEE 45

UL Listed (File No. E3125; Guide No. NLDX, NLDX2, NPKR)

CSA Certified (LR 1234)

CE Marked (Per EN 60947)

ABS American Bureau of shipping

For UL Certifications Directory: <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>