

Product: 505V-FOD-23

Description: 505 NEMA Full Voltage Reversing Starter



Representative
Photo Only (actual product may vary based
on configuration selections)

SYSTEM VOLTAGE DATA	
Phases	3 Phase
STARTER DATA	
NEMA Size	NEMA 5
Enclosure Type	Open
Vertically Arranged Starter	Yes
Coil Voltage	115-120V 60Hz
OPTIONS	
Overload Relay	No Overload Protection
IMPORTANT INFORMATION	
Enclosure Size [length x width x depth]	Open Style / Unknown
CERTIFICATIONS AND APPROVALS	
NEMA/EEMAC	ICS 2 (Industrial Controls and Systems)
UL	508
CSA	22.2, No. 14
ABS	4/5.115
USCG	46 CFR 111.70
IEEE	45
UL	Listed (File No. E3125; Guide No. NLDX, NLDX2, NPKR)
CSA	Certified (LR 1234)
CE	Marked (Per EN 60947)
ABS	American Bureau of shipping
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm