

Product Details and Certifications

Product: 505V-FOD-XXX

Description: 505 NEMA Full Voltage Reversing Starter

SYSTEM VOLTAGE DATA

Phases 3 Phase

STARTER DATA

NEMA Size NEMA 5
Enclosure Type Open
Vertically Arranged Starter Yes
Coil Voltage 115-120V 60Hz

OPTIONS

Overload Relay Provision for Mounting an Overload Relay (field installation)

IMPORTANT INFORMATION

Enclosure Size [length x width x depth] Open Style / Unknown

CERTIFICATIONS AND APPROVALS

NEMA/EEMAC ICS 2 (Industrial Controls and Systems)
UL 508
CSA 22.2, No. 14
ABS 4/5.115
USCG 46 CFR 111.70
IEEE 45
UL Listed (File No. E3125; Guide No. NLDX, NLDX2, NPKR)
CSA Certified (LR 1234)
CE Marked (Per EN 60947)
ABS American Bureau of shipping
For UL Certifications Directory: <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>