

Product: 520E-DOA-XXX

Description: 520E NEMA 2 Speed Separate Winding Starter

SYSTEM VOLTAGE DATA

Supply Voltage 240V 60Hz

MOTOR DATA

Voltage 230V 60Hz

Motor Type Constant or Variable Torque

STARTER DATA

NEMA Size NEMA 3

Enclosure Type Open

Vertically Arranged Starter No

Control Voltage 230-240V 60Hz

OPTIONS

Overload Relay (High Speed) Provision for Mounting an Overload Relay (field installation)

IMPORTANT INFORMATION

Enclosure Size [length x width x depth] Open Style / Unknown

CERTIFICATIONS AND APPROVALS

NEMA/EEMAC ICS (Industrial Controls and Systems)

UL 508

CSA 22.2, No. 14

UL Listed (File No. E3125; Guide No. NLDX)

CSA Certified (LR 1234)

For UL Certifications Directory: <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>