

# Product Details

## Product: 520F-COH

Description: NEMA Starter,2 Speed,Con/Var Torque,SIZE 2, with Eutectic Alloy Overload Relay

### **SYSTEM VOLTAGE DATA**

---

Supply Voltage 208V 60Hz

### **MOTOR DATA**

---

Voltage 200V 60Hz  
Motor Type Constant or Variable Torque  
Horsepower 10 HP

### **STARTER DATA**

---

NEMA Size NEMA 2  
Enclosure Type Open  
Vertically Arranged Starter No  
Control Voltage 200-208V 60Hz

### **OPTIONS**

---

Overload Relay (High Speed) Eutectic Alloy

### **Certifications and Approvals**

---

NEMA/EEMAC ICS (Industrial Controls and Systems)  
UL 508  
CSA 22.2, No. 14  
UL Listed (File No. E3125; Guide No. NLDX)  
CSA Certified (LR 1234)