

# Product Details and Certifications

**Cross Reference RA Part Number: 800F-ATR19L A**

 **Product: 800F-ATR19L**

Description: 800F Reset Rod, 321mm Rod, 35mm Pusher (Threaded Entire Length)



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Accessories	(1) Reset Rod
Packaging	1 per Package

Reset Operators — Mechanical and/or Electrical Reset



**Reset Operator**  
 Cat. No. 800FP-R611

Button Color	Legend Text	Pkg. Quantity	Flush — Round	
			Plastic	Metal
Blue	R	1	Cat. No.	Cat. No.
	No Legend		800FP-R611	800FM-R611
			800FP-R6	800FM-R6

800F  $\frac{M}{a}$  -  $\frac{R}{b}$   $\frac{6}{c}$   $\frac{11}{d}$

*a*

Operator Construction	
Code	Description
P	Round plastic operator (IP66, Type 4/4X/13)
M	Round metal operator (IP66, Type 4/13)

*b*

Operator Type	
Code	Type
R	Reset*§

*c*

Color Cap	
Code	Color
1	White
2	Black
6	Blue

*d*

Legend Text	
Code	Text
Blank	No text
11	R

\* Will accept latch and up to four single circuit contact blocks or two dual circuit contact blocks; no contacts allowed in center position.  
 § 11 mm reset stroke length.

**Threaded Reset Rod Reset Operators**



**Threaded Reset Rod with 35 mm Pusher**  
 Cat. No. 800F-ATR19L

Rod Length [mm]‡	Rod Length Adjustability [mm]	Pkg. Quantity	Threaded Reset Rod	
			10 mm Pusher	35 mm Pusher
			Cat. No.	Cat. No.
40	34...52	1	<b>800F-ATR01</b>	800F-ATR01L
55	50...67		800F-ATR02	800F-ATR02L
85	80...98		<b>800F-ATR04</b>	800F-ATR04L
115	110...128		800F-ATR06	800F-ATR06L
145	141...159		<b>800F-ATR08</b>	800F-ATR08L
<b>315</b>	<b>34...326</b>	§	<b>800F-ATR19</b>	§ <b>800F-ATR19L</b>

‡ If contact blocks are used, they must have a minimum rod length of 55 mm for one level of contact blocks and 85 mm for two levels of contact blocks.  
 § Rod is threaded along its entire length for ease of cutting to desired length.

