


Product Details and Certifications

Cross Reference RA Part Number: 800H-PR16G F

 **Product: 800H-PR16G**

Description: 30.5mm Type 4/4X/13 Pilot Light, Xfmr, No Test Option, Incand., Green, 120V AC 50/60 Hz



Representative Photo Only (actual product may vary based on configuration selections)

PUSH BUTTON DATA

Hazardous Location	No
Finger Safe Guards	No Guards
Power Module Type	Transformer
Lamp Test Options	No Test Option
Illumination Options	Incandescent
Voltage	120V AC 50/60 Hz
Lens Color	Green
Contact Blocks	None

ASSEMBLY

Factory or User Assembled?	Factory Assembled
----------------------------	-------------------

CERTIFICATIONS AND APPROVALS

UL	Listed E14840, E10314; Guide #NKCR, NOIV
CSA	LR1234, LR11924, 22.2 #14
CE	60947-5-1
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

RECOMMENDED SPARE PARTS

800H-N149	LOCKING RING
800H-N146	THRUST WASHER
800H-N148	TRIM WASHER
F-14963	GASKET

