

# Product Details and Certifications

➔ Cross Reference RA Part Number: **800T-J44A T**

➔ Product: **800T-J44A**

Description: 30.5mm Type 4/13 3 Pos. Cyl. Lock Sel. Switch, Maint., Lock  
All, Std. Key, D018 Key



Representative Photo Only (actual product may vary based on configuration selections)

## **SELECTOR SWITCH DATA**

Hazardous Location	No
Finger Safe Guards	No Guards
Operator Function	Maintained
Locking Position	All
Key Type	Standard
Key Options	Std. Key
Target Table Selections	Cam and Contact Blocks
Contact Blocks	1 N.O. - 1 N.C.

## **ASSEMBLY**

Factory or User Assembled?	Factory Assembled
----------------------------	-------------------

## **CERTIFICATIONS AND APPROVALS**

UL	Listed E14840, E10314; Guide #NKCR, NOIV
CSA	LR1234, LR11924, 22.2 #14
CE	60947-5-1
For UL Certifications Directory:	<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>

## **RECOMMENDED SPARE PARTS**

800T-N232	LOCKING RING ①
800T-N293	THRUST WASHER
800T-N292	TRIM WASHER
800T-N19	GASKET
X-181170	Replacement Keys for 800T Cylinder Lock

① Locking Ring repair parts are for Series N and later devices. For illuminated selector switches, see footnote 2.

② Locking Ring repair parts are for Series U units only. For Series T units, replace the entire device

③ Locking Ring repair part contains both the knob/actuator and the locking ring.

The locking ring only is not available separately.

