



CROSS REF FOR  
RA PART NO  
25105-011-10



[Manufacturers](#) [Products](#) [Markets](#) [Locations](#) [Resources](#) [Careers](#) [About Us](#)

[Home](#) [Power Distribution](#) [Circuit Breakers](#) [Circuit Breakers - Bolt-On](#) [2-Pole - 120/240V](#)

Eaton **BAB2060** 60A, 2P, 120/240V, Type BAB, 10 kAIC, CB



Cat: BAB2060  
Mfg: Eaton  
Item: 060459  
UPC: 786679302606

(0) Write a review  
What's your trade slang?

[Catalog Page](#)

**Details**

**Reviews (0)**

60 Amp, 2-Pole, Miniature Industrial Circuit Breaker, Type BAB, Quicklag, Bolt-On, 10 kAIC, 120/240 VAC.

<b>Platt Cat:</b>	CUTBAB2060
<b>Platt Item:</b>	060459
<b>Mfg:</b>	<a href="#">Cutler-Hammer</a> , <a href="#">Eaton</a> , <a href="#">Westinghouse</a>
<b>UPC:</b>	786679302606
<b>Category:</b>	<a href="#">2-Pole - 120/240V</a>
<b>Familystyle:</b>	Quicklag, BAB
<b>Mounting:</b>	Bolt On

<b>Amps:</b>	60
<b>Volts AC:</b>	120, 240
<b>Poles:</b>	2
<b>Type:</b>	Miniature Industrial
<b>Interrupt Rating AC:</b>	10000

- **Category:** [Power Distribution](#) > [Circuit Breakers](#) > [Circuit Breakers - Bolt-On](#) > [2-Pole - 120/240V](#)
- **Products related to** [BAB2060 60A, 2P, 120/240V, Type BAB, 10 kAIC, CB](#) or visit the [Eaton](#) site.
- **For help with** [60A, 2P, 120/240V, Type BAB, 10 kAIC, CB](#) from [Eaton](#), call **Platt at 800-257-5288** from 4a - 8p (pst) 7 days.
- Click "**Add to Cart**" to buy Eaton BAB2060 60A, 2P, 120/240V, Type BAB, 10 kAIC, CB.
- **Also known as:** 786679302606, WHSBAB2060, CUTBAB2060, Eaton, BAB2060, 2-Pole - 120/240V, Circuit Breakers - Bolt-On, Circuit Breakers, Power Distribution, Cutler-Hammer, Westinghouse

## Product Selection

QUICKLAG Type BAB Single-Pole



### QUICKLAG Type: BA 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
10	BAB1010	BAB2010	BAB2010H ③	BAB3010H ③
15	BAB1015 ①②	BAB2015	BAB2015H	BAB3015H
20	BAB1020 ①②	BAB2020	BAB2020H	BAB3020H
25	BAB1025	BAB2025	BAB2025H	BAB3025H
30	BAB1030	BAB2030	BAB2030H	BAB3030H
35	BAB1035	BAB2035	BAB2035H	BAB3035H
40	BAB1040	BAB2040	BAB2040H	BAB3040H
45	BAB1045	BAB2045	BAB2045H	BAB3045H
50	BAB1050	BAB2050	BAB2050H	BAB3050H
55	BAB1055	BAB2055	BAB2055H	BAB3055H
60	BAB1060	<b>BAB2060</b>	BAB2060H	BAB3060H
70	BAB1070	BAB2070	BAB2070H	BAB3070H
80	—	BAB2080	BAB2080H	BAB3080H
90	—	BAB2090	BAB2090H	BAB3090H
100	BAB1100	BAB2100	BAB2100H	BAB3100H
110	—	BAB2110	—	—
125	—	BAB2125	—	—

### QUICKLAG Type: BA Non-Automatic Switches

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
50	BAB1050N	—	BAB2050N	BAB3050N
60	BAB1060N	—	BAB2060N	BAB3060N
100	BAB1100N	—	BAB2100N	BAB3100N

### QUICKLAG Type: QBHW 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
15	QBHW1015 ①	QBHW2015	QBHW2015H	QBHW3015H
20	QBHW1020 ①	QBHW2020	QBHW2020H	QBHW3020H
25	QBHW1025	QBHW2025	QBHW2025H	QBHW3025H
30	QBHW1030	QBHW2030	QBHW2030H	QBHW3030H
35	QBHW1035	QBHW2035	QBHW2035H	QBHW3035H
40	QBHW1040	QBHW2040	QBHW2040H	QBHW3040H
45	QBHW1045	QBHW2045	QBHW2045H	QBHW3045H
50	QBHW1050	QBHW2050	QBHW2050H	QBHW3050H
55	QBHW1055	QBHW2055	QBHW2055H	QBHW3055H
60	QBHW1060	QBHW2060	QBHW2060H	QBHW3060H
70	QBHW1070	QBHW2070	QBHW2070H	QBHW3070H
80	—	QBHW2080	QBHW2080H	QBHW3080H
90	—	QBHW2090	QBHW2090H	QBHW3090H
100	—	QBHW2100	QBHW2100H	QBHW3100H
110	—	QBHW2110	—	—
125	—	QBHW2125	—	—

#### Notes

- ① Switching duty rated for 120 Vac fluorescent light applications.
- ② For special low-magnetic breaker, order **BAB1015L1** or **BAB1020L1**.
- ③ Not UL listed.