

Product Details and Certifications

Product: HPK-B2010C-MA42BA

Description: HPK-Series High Power Asynchronous Motors

PRODUCT SELECTION

Voltage	460 V
FrameSize	2010
RPM	1500 RPM
Feedback	Multi-turn High Resolution Encoder (absolute feedback)
Blower/Junction Box Location	Inline Blower, F3 Junction Box (no brake only)
Connectors	Feedback - Right Angle, 180° Rotatable
BrakeOption	No Brake
MountingType	IEC Metric, Free Mounting Holes (Type FF), Foot Mount Only/Keyed Shaft