

Part #: TCF10

Category: Fuses and Circuit Protection

Manufacturer: Cooper Industries

Description: TIME DELAY BLOW ELECTRIC FUSE, 10A, 600VAC, 300VDC, 300000A (IR), INLINE/HOLDER



› Also on this page: [Distributors](#)

SPECIFICATIONS

Lead Free	Yes
EU RoHS Compliant	Yes
Status	ACTIVE
Rated Current	10 A
Terminal Finish	TIN
Mounting Feature	INLINE/HOLDER
Rated Voltage(AC)	600 V
Rated Voltage(DC)	300 V
Manufacturer Series	TCF
Operating Temperature-Max	65 Cel
Operating Temperature-Min	-10 Cel
Body Height	25.4 mm
Body Length or Diameter	47.75 mm
Body Breadth	19.05 mm
Terminal Shape	TAB/BLADE
Built-in Feature	INDICATOR
Electric Fuse Type	ELECTRIC FUSE
Blow Characteristic	TIME DELAY
Rated Breaking Capacity	300000 V