

**Product:** 800H-NR2KF4B

**Description:** 800H 4 Position Selector Switch

**ASSEMBLY**

Factory or User Assembled?

Factory Assembled

**SELECTOR SWITCH DATA**

Hazardous Location

No

Finger Safe Guards

No Guards

Knob Insert or Metal Wing Lever Color

White

Operator Function

Maintained

Target Table Selections

Cam and Contact Blocks

**CERTIFICATIONS AND APPROVALS**

UL

Listed E14840, E10314; Guide #NKCR, NOIV

CSA

LR1234, LR11924, 22.2 #14

CE

60947-5-1

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

## 3-POSITION SELECTOR SWITCHES, NON-ILLUMINATED

CONTACT CONFIGURATION	OPERATOR TYPE	TYPE 4/13 METAL (800T)			TYPE 4/4X/13 PLASTIC (800H) STANDARD KNOB
		STANDARD KNOB	KNOB LEVER	CYLINDER LOCK	
1 N.O. - 1 N.C.		800T-J2A	800T-J17A	800T-J42A	800H-JR2A
		800T-J4A	800T-J18A	800T-J50A	800H-JR4A
		800T-J5A	800T-J19A	800T-J38A	800H-JR5A
		800T-J91A	800T-J20A	800T-J631A	800H-JR91A

## 3-POSITION SELECTOR SWITCHES, ILLUMINATED

TYPE	OPERATOR TYPE	TYPE 4/13 METAL (800T) STANDARD KNOB	TYPE 4/4X/13 PLASTIC (800H) STANDARD KNOB
		<ul style="list-style-type: none"> <li>UNIVERSAL LED</li> <li>12-130V AC/DC</li> <li>RED KNOB</li> <li>1 N.O. - 1 N.C.</li> </ul>	  
<ul style="list-style-type: none"> <li>TRANSFORMER</li> <li>RED LED</li> <li>120V AC, 50/60 HZ</li> <li>1 N.O. - 1 N.C.</li> </ul>	  	800T-16JRH2KB7AX 800T-16JRH4KB7AX 800T-16JRH5KB7AX	800H-16JRRH2KB7AX 800H-16JRRH4KB7AX 800H-16JRRH5KB7AX

## 4-POSITION SELECTOR SWITCHES, NON-ILLUMINATED

CONTACT CONFIGURATION	OPERATOR TYPE	TYPE 4/13 METAL (800T)			TYPE 4/4X/13 PLASTIC (800H) STANDARD KNOB
		STANDARD KNOB	KNOB LEVER	CYLINDER LOCK	
2 N.O. - 2 N.C.		800T-N2KF4B	800T-N17KF4B	800T-N33KF4B	800H-NR2KF4B
		800T-N3KF4B	800T-N29KF4B	800T-N133KF4B	800H-NR3KF4B
		800T-N9KF4B	800T-N30KF4B	800T-N233KF4B	800H-NR9KF4B