



TITLE: 3PH DISTRIBUTION TRANSFORMER	
NAMEPLATE INFORMATION	
NO.	1
DATE	17/03/20
BY	GC
REVISION	CHANGED DESIGN DIMENSIONS
SCALE:	DES: GCALOTA
NTS	DATE: 17/03/20

SHEET 1 OF 2
EDB 221243

→ Cross Reference RA Part Number PN-419533

THREE PHASE DRY TYPE TRANSFORMER
ALLEN-BRADLEY
MILWAUKEE, WI. USA

ALLEN BRADLEY CAT. No.

PN-419533



LR3902



E112313

kVA

CLASS

TYPE

TEMP. RISE °C

TEMP. CLASS °C

FREQ. Hz

IMPEDANCE %
@ 100 °C

ENCL. TYPE

WEIGHT LBS

PART NO.


SERIAL NO:


cab3084e

VOLTS	% RATED VOLTAGE	CONNECTION
504	105	1
492	102.5	2
480	100	3
468	97.5	4
456	95	5


V	<input type="text" value="480V"/>	<input type="text" value="480Y/277V"/>
kV BIL	<input type="text" value="-"/>	<input type="text" value="-"/>
	<input type="text" value="H1 H2 H3"/>	<input type="text" value="X0 X1 X2 X3"/>

ENERGY EFFICIENCY





FRONT_VIEW



SIDE_VIEW

0.50-13
UNC (4)



Hammond Power Solutions Inc.

TITLE: 3PH DISTRIBUTION TRANSFORMER

NO.	DATE	BY	REVISION	SCALE:
1	17/03/20	GC	CHANGED DESIGN DIMENSIONS	NTS

DES: GCALOTA
DATE: 17/03/10

SHEET 2 OF 2

EDB 221243

1.0 root 2017/03/20 14:10