

# CROSS TO PN-61749

## Product Details and Certifications

**Product:** 20F11ND8P0AA0NNNNN

Description: PowerFlex 753 AC Drive, with Embedded I/O, Air Cooled, AC Input with DC Terminals, Open Type, 8 Amps, 5HP ND, 5HP HD, 480 VAC, 3 PH, Frame 2, Filtered, CM Jumper Removed, DB T ransistor, Blank (No HIM)



Representative Photo Only (actual product may vary based on configuration selections)

### **BASE DRIVE INFORMATION**

Bulletin Number	PowerFlex 753 AC Drive, with Embedded I/O
Voltage Class	480 VAC, 3 PH
Current / Power Rating	8 Amps, 5HP ND, 5HP HD
Enclosure Type	Open Type
Input Type	AC Input with DC Terminals
Frame Size	Frame 2
Filtering & CM Cap Config	Filtered, CM Jumper Removed
Dynamic Braking	DB T ransistor

### **Recommended Spare Parts**

20-750-2262C-2R	1	PF750-24V I/O Module-2AI,2AO,6DI,2RO
20-750-2262D-2R	1	PF750-115V I/O Module-2AI,2AO,6DI,2RO
20-750-2263C-1R2T	1	PF750-24V I/O Module-2AI,2AO,6DI,1RO,2TO
20-750-ENC-1	1	PF750 Incremental Encoder Module
20-750-DENC-1	1	PF750 Dual Incremental Encoder Module
20-750-UFB-1	1	PF750 Universal Feedback Module
20-750-APS	1	PF750 24V Aux Power Supply Module
20-750-S	1	PF750 Safe Torque Off Module
20-750-S1	1	PF750 Safe Speed Monitor Module
20-750-DB1-D2	1	PF750 Int Brake Resistor, 400/480V, Fr 2
20-750-FLNG1-F2	1	PF750 Flange Adapter, Type 1, Frame 2
20-750-EMC1-F2	1	PF750 EMC Plate & Cores, Frame 2
20-750-EMC2-F2	1	PF750 EMC Cores, Frame 2
20-750-NEMA1-F2	1	PF750 NEMA 1 Kit, Frame 2
20-750-CNETC	1	PF750-Series ControlNet Coax
20-750-DNET	1	PowerFlex 750-Series DeviceNet Option Card
20-750-20COMM	1	PowerFlex 750-Series 20-COMM-* Adapter Card
20-HIM-A6	1	PowerFlex Architecture Class Enhanced HIM, NEMA 1
20-HIM-C6S	1	PowerFlex Architecture Class Remote Enhanced HIM, IP66 (NEMA 4X/12) Indoor Use Only

SK-R1-MCB1-PF753	1	PF753 Main Control Board
SK-R1-TB-PF753	1	PF753 Main Control Board Terminal Blocks
SK-R1-POD1	1	PF750 Control Pod, Frames 2-7
SK-R1-BP1	1	PF750 Backplane Interface
SK-R1-CR1	1	PF750 Pod HIM Cradle
SK-R1-PC1	1	PF750 Power Interface Cable
SK-R1-PJ1-F25	1	PF750 Power Jumper Screws, Frames 2 - 5
SK-R1-TB-2262	1	PF750 2262 I/O Terminal Blocks
SK-R1-TB-APS	1	PF750 APS Terminal Block
SK-R1-TB-S	1	PF750 Safe Torque Off Terminal Block
SK-R1-TB-S1	1	PF750 Safe Speed Monitor Terminal Blocks
SK-R1-TB-ENC-1	1	PF750 Single Encoder Terminal Block
SK-R1-TB-DENC-1	1	PF750 Dual Encoder Terminal Block
SK-R1-CVR1-F2	1	PF750 Open / NEMA 1 Cover, Fr 2
SK-R9-CHSS1-F2	1	PF750 Open / NEMA 1 Chassis, Fr 2
SK-R9-FAN11-F2	1	PF750 Opn/N1 HSFan,F5,400-480V up to 75HP
SK-R9-FAN2-F23	1	PF750 Internal Fan Kit, Frames 2 and 3