

Hammond SP5000MQMJ HT5196 - Control Transformer 240x480V Pri 120x240V Sec - 5000VA - 50/60Hz - 1 Phase - HPS Spartan

CROSS REFERENCE TO ROCKWELL PART NUMBER PN-90796



- Supplied with trilingual installation and wiring instruction sheets
- Molded terminal blocks for primary and secondary connections (1)
- Optional finger guards available (1)
- Optional fuse block adapter kit available (1)
- Premium Packaging which features:
 - Premium fluted cartons
 - Custom molded foam inserts
 - Easy removal and repacking
 - Industry's best box label
- Superior insulating materials. The HPS Spartan series transformers offer the following insulation systems:
 - 2000 VA to 5000 VA: 115°C rise, 180°C temperature class (F)
 - Up to 1500 VA: 80°C rise, 130°C temperature class (B)

(1) up to and including 3000VA or 30 amps

Product information

Model:	
Brand	Hammond Power Solutions
Mfg part number	SP5000MQMJ
Specifications:	
Transformer subcategory	Control
Electrical Specifications:	
Phase	Single
Frequency (Hz)	50/60
kVA	5
K rating	1
Primary configuration	Two Winding
Secondary configuration	Two Winding
Reverse connectable	Yes
Winding material	Copper
Electrostatically shielded	No
Connection type	Screw Terminals
Mechanical Specifications:	
Temperature rise (deg C)	115
Insulation system (deg C)	180
Construction style	Open - Core & Coil
Mounting type	Base/Panel
Cooling	Air/Dry
Product Features:	
UL listed	Yes
CSA approved	Yes
Agency approvals	IEC 61558, NEMA (ST-1), CE Marked, ROHS Compliant