

**K-Frame**

**100% Rated Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug**

Order as individual components: Breaker Frame (which includes Trip Unit), Rating Plug, Terminals.

**Table 12-80. 100% Rated Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug**

Maximum Continuous Ampere Rating @ 40°C	Circuit Breaker Frame Only						Digitrip OPTIM Rating Plug Only	
	L – Adjustable Long Delay Pickup (I <sub>p</sub> ) with Adjustable Long Delay Time (I <sup>2</sup> t or I <sup>4</sup> t Response) ①						Ampere Rating	Fixed Rating Plug
	S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I <sup>2</sup> t or Flat Response)							
	I – Adjustable Instantaneous Pickup							
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I <sup>2</sup> t or Flat Response)								
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I <sup>2</sup> t or Flat Response)								
OPTIM 550 ②								
LSI		LSIG		LSIA				
Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	

**3-Pole Standard Interrupting Capacity 600V AC Rated 35 kAIC @ 480V AC**

125	CKD3125T52W	3,905.	CKD3125T56W	4,715.	CKD3125T57W	4,245.	70	ORPK125A70	112.
							90	ORPK125A90	112.
							100	ORPK125A100	112.
							110	ORPK125A110	112.
							125	ORPK125A125	112.
250	CKD3250T52W	4,815.	CKD3250T56W	6,160.	CKD3250T57W	5,550.	125	ORPK025A125	112.
							150	ORPK025A150	112.
							175	ORPK025A175	112.
							200	ORPK025A200	112.
							225	ORPK025A225	112.
							250	ORPK025A250	112.
400	CKD3400T52W	4,815.	CKD3400T56W	6,160.	CKD3400T57W	5,550.	200	ORPK40A200	112.
							225	ORPK40A225	112.
							250	ORPK40A250	112.
							300	ORPK40A300	112.
							350	ORPK40A350	112.
							400	ORPK40A400	112.

**3-Pole High Interrupting Capacity 600V AC Rated 65 kAIC @ 480V AC**

125	CHKD3125T52W	6,110.	CHKD3125T56W	6,930.	CHKD3125T57W	6,510.	70	ORPK125A70	112.
							90	ORPK125A90	112.
							100	ORPK125A100	112.
							110	ORPK125A110	112.
							125	ORPK125A125	112.
250	CHKD3250T52W	7,020.	CHKD3250T56W	8,380.	CHKD3250T57W	7,700.	125	ORPK025A125	112.
							150	ORPK025A150	112.
							175	ORPK025A175	112.
							200	ORPK025A200	112.
							225	ORPK025A225	112.
							250	ORPK025A250	112.
400	CHKD3400T52W	7,020.	CHKD3400T56W	8,380.	CHKD3400T57W	7,700.	200	ORPK40A200	112.
							225	ORPK40A225	112.
							250	ORPK40A250	112.
							300	ORPK40A300	112.
							350	ORPK40A350	112.
							400	ORPK40A400	112.

① Long delay I<sup>4</sup>t response selection limits short delay time to flat response.

② Zone Interlocking, PowerNet, or both features can be added at the factory by adding Suffixes **ZG**, **PN** or **ZGP** respectively to above Catalog Number (Refer to Page 12-184 and take list price Adder x 1.25).

**Note:** Instruction Leaflet/FRED Number 29C104.

12

