

→ Cross Reference RA Part Number PP7375

Allen-Bradley Traymount® TAPM63060-3 ←



PRODUCT DIMENSIONS

- ◆ Enclosure Size: 8.75 in x 15.50 in x 8.50 in
- ◆ Weight: 45

PART NUMBER SPECIFICATIONS

- ◆ kVAR: 60
- ◆ Voltage: 600
- ◆ Frequency(Hz): 60
- ◆ Amps: 58

APPLICATIONS

- ◆ At the load within Motor Control Centers (MCCs)

STANDARD FEATURES

- ◆ UL recognized component
- ◆ 2-year warranty
- ◆ 3-line fusing
- ◆ Discharge resistors per NEC requirements
- ◆ Assembled in the USA

CAPACITOR CELLS

- ◆ 20-year rated life
- ◆ 5-year warranty
- ◆ Self-contained, 3-phase, delta-connected
- ◆ Industrial grade dry-type construction
- ◆ Losses of less than ½ watt per kVAR
- ◆ Self-healing metallized polypropylene dielectric film
- ◆ 3-phase pressure-actuated interrupter
- ◆ Hermetically sealed steel case
- ◆ Threaded insulated terminals

INDICATION

- ◆ Fusing without indication

FUSES

- ◆ Fast-acting, current-limiting, with 200,000 ampere interrupting capacity

FIELD WIRING TERMINATION

- ◆ Mechanical connections are provided for all field wiring termination points

OPTIONS

- ◆ Other voltages and frequencies available
- ◆ Other kVAR configurations available