

UNIT SPECIFICATIONS:					
KVAR	HARMONIC	VOLT	HZ	PHASE	HP
3	5TH	480	60	3	7.5
ENCLOSURE		WHITE OPEN PANEL			
APPROX.WT. LBS.		40			


SYMBOL	TCI PART NUMBER
LR	KDRC1T
TR	KTR3A65HG
CAP.	16446
Fu1, 2, 3	11262

PB—POWER INPUT BLOCK:
 WIRE RANGE—#18 TO #4 AWG.
 TIGHTENING TORQUE 20 IN—LB.

GROUND LUG:
 WIRE RANGE—1/0 TO #14 AWG.
 TIGHTENING TORQUE 200 IN—LB.

CUSTOMER IS RESPONSIBLE FOR PROPER COOLING OF FILTER COMPONENTS.
 CAPACITORS MAXIMUM AMBIENT 50°C

CUSTOMER IS RESPONSIBLE FOR INSTALLATION TO MEET ALL NATIONAL AND LOCAL ELECTRICAL CODES.

TOLERANCES EXCEPT AS NOTED				 7878 N. 86th STREET MILWAUKEE, WI 53224
DECIMAL				
.XX ± .03 .XXX ± .01				
FRACTIONAL ± 1/32				HG8AW00ST, HG7 STANDARD 7.5 HP, 480/3/60, OPEN
ANGULAR ± 1/2°				
△ MOVED POWER BLOCK	2/21/06	DSW	BY	DRN BY DSW DATE 03/02/05 SCALE TO FIT APPROV. B
NO REVISION	DATE	BY		DWG. NO. 102535DG SHT. 1 of 1