

COPY A

**ACCESSORY KITS FOR FIELD INSTALLATION  
SIZE 5 - SERIES LETTER L AND LATER APPLICATION ONLY  
OPEN TYPE DEVICES ONLY**

**Bulletin Numbers:** 500 & 500F  
500L & 500FL  
509 With Bulletin No. 592 Overload Relay  
509 With Bulletin No. 593 Overload Relay

**Auxiliary Contacts**

Single Circuit (1 N.O.).....Catalog No. 595-A  
Single Circuit (1 N.C.).....Catalog No. 595-B  
Single Circuit (1 N.C. Late Break).....Catalog No. 595-BL  
Double Circuit (2 N.O.).....Catalog No. 595-AA  
Double Circuit (2 N.C.).....Catalog No. 595-BB  
Double Circuit (1 N.O.-1 N.C.).....Catalog No. 595-AB

**Tie Point Terminal**.....Catalog No. 599-TP34  
**Top Wiring Terminal Kit (3 Terminals)** [1].....Catalog No. 599-TW5P  
**Control Circuit Fusing Kit (Single Pole) - Controller or Panel Mounted** [2]

(Rejection Type Fuse Only) [3].....Catalog No. 599-FR04  
**NOTE:** Each kit occupies the space of one double circuit auxiliary contact block when controller mounted.

**Surge Suppressor**

(120 Volt AC Maximum).....Catalog No. 599-K04  
(240 Volt AC Maximum).....Catalog No. 599-KA04

**Device Markers (50 Markers)**.....Catalog No. 599-DM [4] 5

**Timer Attachment** [5]

**On Delay**  
(Left Side Controller Mounted).....Catalog No. 596-TL32  
**On Delay**  
(Right Side Controller Mounted).....Catalog No. 596-TR32  
**Off Delay**  
(Left Side Controller Mounted).....Catalog No. 596-TL33  
**Off Delay**  
(Right Side Controller Mounted).....Catalog No. 596-TR33

**Note:** Occupies space of two adjacent double circuit auxiliary contact blocks when mounted.

**Auxiliary Contact For Bulletin 592 Overload Relay**.....Catalog No. 595-A02

- [1] Not applicable to Bulletin Numbers 500, 500L & 500FL.
- [2] May be used when additional control circuit overcurrent protection is required. Refer to the National Electrical Code.
- [3] For use on a circuit capable of delivering no more than 200,000 RMS symmetrical amperes, 600 volts maximum.
- [4] To complete Catalog number, insert in third position the desired numeric symbol (0 through 9) or one of the following letters: A, B, C, D, E, F, H, L, M, P, R, S, T, U, or W.
- [5] Timing range 0.1 to 180 seconds (adjustable).

40051-716-01 (B)  
Printed in U.S.A.



COPY B



-01	B	ONE SIDE PRINTED BODY STOCK WHITE BODY INK BLACK	3-1/4" W X 4-1/2" H FOLDED
PART NO.	CHG. LTR.	MATERIAL	FINISHED SIZE

**DO NOT WRITE IN THIS AREA.**

REFERENCES		ACCESSORY KITS FOR FIELD INSTALLATION - SIZE 5		WAS	
REVISION	DIMENSIONS APPLY BEFORE SURFACE TREATMENT	SERIES LETTER L AND LATER APPLICATION ONLY.		ALLEN-BRADLEY MILWAUKEE, WISCONSIN	
RELEASE	(DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED	CONTENTS FOR INSTRUCTION SHEET			
1 5174-82	2 PLACE DECIMAL (XX)	"500+ LINE"			
2 1852-88	±	DR. <i>Kathy Fitch</i>	DATE 10-19-82	SHEET 1 OF 1	
	3 PLACE DECIMAL (XXX)	CHKD. <i>Shawn Hubanks</i>	DATE 10-20-82	DWG. SIZE	
REFER. BOOK	ANGLES ±	APPD. <i>m Robinson</i>	DATE 10/22/82	B 40051-716	