



Circuit Breaker Time/Current Curves

G-Frame Circuit Breakers

Catalog Types GB, GC, 15-100 Amperes, 2 and 3 Poles, 240 Volts Ac Max.
Catalog Types GHB, GHC, 15-100 Amperes, 2 and 3 Poles, 277/480 Volts Ac Max.

For application and coordination purposes only. Based on 40°C ambient, cold start. Connected with four (4) feet of rated wire (60/75°C) per terminal. Tested in open air with current in all poles.

Maximum Volts	
Breaker Type	Ac Volts
GB, GC	240
GHB, GHC	277/480

Breaker Rating	
Continuous Amperes	Instantaneous Trip, Amperes
15-100	See Curve

Interrupting Rating (UL Listed)		
Breaker Type	Symmetrical RMS Amperes	
	240 Volts	277/480 Volts
GB, GC	65,000	—
GHB, GHC	65,000	14,000