



# Series C Molded Case Circuit Breakers 125 – 600 Amperes

March 2009

L-Frame

**Table 12-215. Types LDB, HLDB and LDCB Electronic Circuit Breakers with Non-Interchangeable Electronic Trip Units Suitable for Reverse Feed**  
Page 12-121

Maximum Continuous Ampere Rating at 40°C ②	Number of Poles	Circuit Breaker Frame Including DigiTrip RMS 310 Electronic Trip Unit Less Terminals and Rating Plug				Digitrip RMS 310 Rating Plug (Order as Separate Items)	
		L – Adjustable Long Delay Pickup (By Adjustable Rating Plug) S – Adjustable Short Delay Pickup with Fixed Short Delay Time (I <sup>2</sup> t Response) or Adjustable Short Time (Flat Response) I – Adjustable Instantaneous Pickup by Setting Short Time Delay Time to Instantaneous G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Delay (Flat Response)				Fixed	Adjustable
		Catalog Number					
LS	LSI	LSG	LSIG	Catalog Number			
Short Time Range		2 – 8 x I <sub>n</sub>	2 – 8 x I <sub>n</sub>	2 – 8 x I <sub>n</sub>	2 – 8 x I <sub>n</sub>		
Short Time Delay		—	0 – 300 ms	—	0 – 300 ms		
Ground Fault Pickup		—	—	Varies by Frame	Varies by Frame		
Ground Fault Delay		—	—	0 – 500 ms	0 – 500 ms		

**Type LDB, HLDB and LDCB with Digitrip 310 Non-Interchangeable Trip Unit**

Rating	Poles	Frame	Frame	Frame	Frame	Rating Plug	Rating Plug
600	3	LDB3600FT33W	LDB3600FT32W	LDB3600FT35W	LDB3600FT35W	6LES300T 6LES350T 6LES400T 6LES450T 6LES500T 6LES600T	300/400/500/600 <b>A6LES600T1</b> 420/440/460/480 <b>A6LES400T5</b> 520/540/560/580 <b>A6LES500T5</b>
600	3	HLDB3600FT33W	HLDB3600FT32W	HLDB3600FT35W	HLDB3600FT36W	6LES300T 6LES350T 6LES400T 6LES450T 6LES500T 6LES600T	300/400/500/600 <b>A6LES600T1</b> 420/440/460/480 <b>A6LES400T5</b> 520/540/560/580 <b>A6LES500T5</b>
600	3	LDCB3600FT33W	LDCB3600FT32W	LDCB3600FT35W	LDCB3600FT36W	6LES300T 6LES350T 6LES400T 6LES450T 6LES500T 6LES600T	300/400/500/600 <b>A6LES600T1</b> 420/440/460/480 <b>A6LES400T5</b> 520/540/560/580 <b>A6LES500T5</b>

① See Table 12-216 on Page 12-121 for prices.

② For ac use only.

**Table 12-216. Type NGC Very High Capacity — U<sub>e</sub> Max. 690 Vac, 100 kA I<sub>CU</sub> at 480 Vac or 415 Vac Prices**

Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$
A6LES400T5 A6LES500T5 A6LES600T1		HLDB3600FT32W HLDB3600FT33W HLDB3600FT35W		HLDB3600FT36W LDB3600FT32W LDB3600FT33W		LDB3600FT35W LDB3600FT36W LDCB3600FT32W	
LDCB3600FT33W LDCB3600FT35W LDCB3600FT36W		6LES300T 6LES350T —		6LES400T 6LES450T —		6LES500T 6LES600T —	

Discount Symbol ..... CB-2