



Littelfuse
UL Class J Fuses, JTD_ID Series

ITEM # JTD100ID

MFG # JTD100ID

Series JTD_ID

Fuse, 100 Amps, 600 VAC

]

1

OVERVIEW

SPECIFICATIONS

DOCS & LINKS

ACCESSORIES

Specifications for Littelfuse JTD100ID

Item Number:	JTD100ID
Manufacturer:	Littelfuse
Item Category:	Fuses
Subcategory:	UL Class J
Series:	JTD_ID
Amps:	100
Volts AC:	600
Volts DC:	300
Characteristic:	Time Delay
Package Type:	Center Bladed
Interrupt Rating:	300KA @ 600V
Trip Indicator:	Yes
Alarm Contact:	No
RoHS:	No
Approvals:	UL;CSA
Length (mm):	117.5 MilliMeters
Diam. (mm):	28.6 MilliMeters
Body Length (mm):	66.7 MilliMeters
Mounting Centers (mm):	89.7;94.5 MilliMeters
Diam. (in):	1.13 Inches
Length (in.):	4.63 Inches
Body Length (in.):	2.63 Inches
Mounting Centers:	3.53;3.72 Inches
Picture No.:	LF_FUSE_ULJ_JTD_ID_70-100A