



**Littelfuse**  
**UL Class J Fuses, JTD\_ID Series**

**ITEM #** JTD175ID

**MFG #** JTD175ID

**Series** JTD\_ID

Fuse, 175 Amps, 600 VAC

O

or

F:

it:

...]



**Specifications for Littelfuse JTD175ID**

<b>Item Number:</b>	JTD175ID
<b>Manufacturer:</b>	Littelfuse
<b>Item Category:</b>	Fuses
<b>Subcategory:</b>	UL Class J
<b>Series:</b>	JTD_ID
<b>Amps:</b>	175
<b>Volts AC:</b>	600
<b>Volts DC:</b>	500
<b>Characteristic:</b>	Time Delay
<b>Package Type:</b>	Center Bladed
<b>Interrupt Rating:</b>	300KA @ 600V
<b>Trip Indicator:</b>	Yes
<b>Alarm Contact:</b>	No
<b>RoHS:</b>	No
<b>Approvals:</b>	UL;CSA
<b>Length (mm):</b>	146.1 MilliMeters
<b>Diam. (mm):</b>	38.1 MilliMeters
<b>Body Length (mm):</b>	76.2 MilliMeters
<b>Mounting Centers (mm):</b>	108.7;113.5 MilliMeters
<b>Diam. (in.):</b>	1.5 Inches
<b>Length (in.):</b>	5.75 Inches
<b>Body Length (in.):</b>	3 Inches
<b>Mounting Centers:</b>	4.28;4.47 Inches
<b>Picture No.:</b>	LF_FUSE_ULJ_JTD_ID_110-200A