



**Product Number: 7ARL-101**



**Indoor, Current Transformer, Model 7ARL, Window ( 2.50" ) Type, 600 volt class, with 100:5 A Ratio**

**An extensive range of indoor current transformers for metering and relaying applications. All of current transformers have a 105°C or higher insulation system and most models are UL recognized.**

**Product Specifications**

|  |   |
|--|---|
| <b>Phase</b>                                   | 1   |
| <b>Environment</b>                             | Indoor  |
| <b>Voltage Class</b>                           | 600   |
| <b>Application</b>                             | Revenue Metering & Relaying   |
| <b>Model Selection Instruction:</b>            | Only choose the model if you are sure this is the product you want as it significantly reduces your selection options. If you do choose Model click search after this selection and then proceed. |
| <b>Model</b>                                   | 7ARL  |
| <b>Design / Form</b>                           | Window  |
| <b>Current Ratio</b>                           | 100:5   |
| <b>Multi Ratio</b>                             | No  |
| <b>Window size</b>                             | 2.01 to 2.50 Inches   |
| <b>Other Description</b>                       | Wire Leads / No Mounting  |
| <b>Window Dimensions</b>                       | 2.50"   |
| <b>IEEE / ANSI Metering Class @ 60Hz B 0.1</b> | 1.2   |
| <b>IEEE / ANSI Metering Class @ 60Hz B 0.2</b> | 4.8   |
| <b>Thermal Rating Factor @ 30°C</b>            | 2.0   |
| <b>Thermal Rating Factor @ 55°C</b>            | 2   |
| <b>Weight (lbs)</b>                            | 1.5   |
| <b>GO Code</b>                                 | GOI01   |