

Auxiliary Switch and Alarm Switch Combination

Table 12-409. F-Frame Auxiliary Switch and Alarm Switch Combination

Mounting Location (Pole)	Factory Mounted						Field Mounted			
	Connection Type and Location						Field Installation Kits ①			
	18-Inch (457 mm) Pigtail Leads				Terminal Block		Pigtail Leads		Terminal Block	
	Same Side		Rear ②		Same Side					
Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	
Left ②	C01		C02		C03		AAL1LPK		AAL1LTK	
Right	C04		C05		C06		AAL1RPK		AAL1RTK ③	

① Not listed with Underwriters Laboratories for field installation.
 ② Standard mounting location.
 ③ Not for use on 4-pole circuit breakers

Table 12-410. F-Frame HMCP Auxiliary Switch and Alarm Switch Combination

Mounting Location (Pole)	Factory Mounted						Field Mounted			
	Connection Type and Location						Field Installation Kits ④			
	18-Inch (457 mm) Pigtail Leads				Terminal Block		Pigtail Leads		Terminal Block	
	Same Side		Rear ⑤		Same Side					
Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	
Left ⑥	C01		C02		C03		MAAL1LPK		MAAL1LTK	
Right	C04		C05		C06		MAAL1RPK		MAAL1RPK	

④ Not listed with Underwriters Laboratories for field installation.
 ⑤ Standard mounting location.
 ⑥ Not for use on 4-pole circuit breakers

12

Table 12-411. J-Frame and HMCP (J) Auxiliary Switch and Alarm Switch Combination

Number of Sets of Contacts (1A and 1B) (1M – 1B)	Mounting Location (Pole)	Factory Mounted						Field Mounted					
		Connection Type and Location						Field Installation Kits ⑦					
		18-Inch (457 mm) Pigtail Leads				Terminal Block		Pigtail Leads		Terminal Block			
		Same Side		Rear ⑧		Opposite Side		Same Side					
Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$		
1	Left Right ⑨	C01 C04		C02 C05		— —		C03 C06		AAL2LPK AAL2RPK		AAL2LTK AAL2RTK ⑩	

⑦ Listed with Underwriters Laboratories for field installation of interchangeable trip unit breakers under E64983.
 ⑧ Standard mounting location — leads exit rear of breaker.
 ⑨ Not for use on 4-pole circuit breakers.

Table 12-412. K-Frame and HMCP (K) Auxiliary Switch and Alarm Switch Combination

Number of Sets of Contacts (1A and 1B) (1M – 1B)	Mounting Location (Pole)	Factory Mounted						Field Mounted					
		Connection Type and Location						Field Installation Kits ⑪					
		18-Inch (457 mm) Pigtail Leads				Terminal Block		Pigtail Leads		Terminal Block			
		Same Side		Rear ⑫		Opposite Side		Same Side					
Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Suffix Number	Adder U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$		
1	Left Right ⑬⑭	C01 C04		C02 C05		— —		C03 C06		AAL3LPK AAL3RPK ⑮		AAL3LTK AAL3RTK	

⑪ Listed with Underwriters Laboratories for field installation of interchangeable trip unit breakers under E64983.
 ⑫ Standard mounting location — leads exit rear of breaker.
 ⑬ Breakers with K-Frame OPTIM 550 can only accept accessories in left pole.
 ⑭ Will not install on OPTIM Trip (RH).