



Hammond Power Solutions Inc.

TITLE: 3 PH DISTRIBUTION TRANSFORMER.
NAMEPLATE INFORMATION

2	05/11/24	SC	HEIGHT REVISED	DES: LRIOLA
1	05/11/24	SC	HEIGHT REVISED	DATE: 04/09/22
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 2

EDB154402200

2.0 jwen 2009/08/12 16:55

THREE PHASE DRY TYPE TRANSFORMER
ALLEN-BRADLEY
MILWAUKEE, WI. USA



LR3902



E112313

P/N 40022-052-09

KVA 25

CLASS AA

TYPE J

TEMP. RISE °C 80

TEMP. CLASS °C 180

FREQ. Hz 60

IMPEDANCE % @ 100 °C 3.2

ENCL. TYPE -

WEIGHT LBS 300

INS. SYSTEM 180-1


SERIAL NO:


cab3001e

VOLTS	% RATED VOLTAGE	CONNECTION
630	105	1-2
615	102.5	2-3
600	100	3-4
585	97.5	4-5
570	95	5-6


154402200
REV. G

HV 600 V
LV 208Y/120
BILL kV -
H1 H2 H3
X0 X1 X2 X3





FRONT_VIEW



SIDE_VIEW



TITLE: 3 PH DISTRIBUTION TRANSFORMER.
TERMINATION DETAILS

2	05/11/24	SC	HEIGHT REVISED	DES: LRIOLA
1	05/11/24	SC	HEIGHT REVISED	DATE: 04/09/22
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 2 OF 2

EDB154402200

2.0 j.wen 2009/08/12 16:55