



Hammond Power Solutions Inc.

TITLE: 3 PH DISTRIBUTION TRANSFORMER
NAMEPLATE INFORMATION

NO.	DATE	BY	REVISION	DES: MCHRIST
				DATE: 05/11/18
				SCALE: NTS

SHEET 1 OF 2

EDB154505900

0.0 schhibb 2010/12/07 12:00

THREE PHASE DRY TYPE TRANSFORMER
ALLEN-BRADLEY
MILWAUKEE, WI. USA



LR3902



E112313

P/N

40022-052-10

KVA 30

CLASS AA

TYPE J

TEMP. RISE °C 80

TEMP. CLASS °C 180

FREQ. Hz 60

IMPEDANCE % @ 100 °C 2.9

ENCL. TYPE -

WEIGHT LBS 300

INS. SYSTEM 180-1

SERIAL NO:

cab3001e

VOLTS	% RATED VOLTAGE	CONNECTION
630	105	1-2
615	102.5	2-3
600	100	3-4
585	97.5	4-5
570	95	5-6

154505900
REV. G


HV

600

V

BILL kV


H1 H2 H3




LV


208Y/120

X0 X1 X2 X3





FRONT_VIEW



SIDE_VIEW



TITLE: 3 PH DISTRIBUTION TRANSFORMER
TERMINATION DETAILS

				DES: MCHRIST
				DATE: 05/11/18
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 2 OF 2

EDB154505900

0.0 schhibb 2010/12/07 12:00