

CROSS REF
FOR
80164-195-01



*Stock Photo

VIEW LARGER

**Idec
Pilot Lights, AP Series**

ITEM # AP6M166-G

MFG # **AP6M166-G**

Series AP

Pilot Light, Grn, 6VDC Direct, LED Full Voltage, 16mm Mounting, LED Flat Lens, 0.110" Terminals

[\[More ...\]](#)

ORDER TODAY: *Est. Lead Time 15 days*
or

FOR IMMEDIATE DELIVERY: **See Alternatives**

Unit Price:	\$ 7.30
10 - 24:	\$ 6.74
25 - 49:	\$ 6.26
50 - 99:	\$ 5.84
100 +:	\$ 5.48

QTY.

Specifications for Idec AP6M166-G

Item Number: **AP6M166-G**
Manufacturer: Idec
Item Category: Pilot Lights
Series: AP
Mounting Size (mm): 16 Millimeters
Lens/Button Shape: Flat Round
Lens/Button Color: Green
Lamp Type: LED
Illumination Voltage: 6V DC
Illumination Circuit: Full Voltage
Terminal Type: Solder/Q.C.
Bezel: Round Plastic
IEC Rating: IP65
Approvals: UL; CSA; CE
Depth Behind Panel: 0.85 Inches
Picture No.: IDEC_INDI_AP6M1-FV-G
Comments: Built-in current limiting resistor.