

Select the starter package that meets your specifications...

Standard products...



Full Voltage, Non-Reversing



Full Voltage, Reversing



Wye-Delta Closed Transition

Benshaw starters are built and tested to UL, IEC and NEMA standards and are supplied with hinged cover, industrial enclosures. Each Benshaw starter is supplied with motor thermal overload protection standard. Options are available for advanced motor/system protection, pilot devices and other optional accessories.

Standard ratings

- ◆ 1/2 thru 600 HP
- ◆ 120 thru 600 V
- ◆ Single or three-phase
- ◆ UL/CSA, IEC and NEMA

Full range of standard starters

- ◆ Full Voltage, Non-Reversing
- ◆ Full Voltage, Reversing
- ◆ 2-Speed, 1 Winding
- ◆ 2-Speed, 2 Windings
- ◆ Part Winding
- ◆ Wye-Delta Open Transition
- ◆ Wye-Delta Closed Transition

Standard combination starters

- ◆ Circuit breakers
- ◆ Non-fused disconnect switches
- ◆ Fused disconnect switches
- ◆ Rotary or flanged operators

Pre-engineered starter options

- ◆ N1, 12, 3R, 4 enclosures
- ◆ Full range of control options
- ◆ Metering packages
- ◆ Advanced motor/system protection
- ◆ Oversized enclosures
- ◆ Control voltage options

Pre-engineered industry-specific solutions

- ◆ Pump control starters
- ◆ Compressor starters
- ◆ Chiller starters
- ◆ Motor-mounted starters
- ◆ Inverter bypass units