



ALL DIMENSIONS ARE IN INCHES
 * TOLERANCES STD. + / - 0.1 INCHES [+ / - 3 MM]

- * OPTIONAL FUSEBLOCK ADAPTER KIT (P/N SPFBAK1) WILL ADD 0.38"[9.65] TO THE HEIGHT
- * OPTIONAL PRIMARY AND SECONDARY FINGERSHIELDS (P/N SPFG1) WILL ADD 0.19"[4.9] TO THE HEIGHT AND 0.38"[9.65] TO THE DEPTH

<p>Hammond Power Solutions Inc.</p> <p>HPS SPARTAN INDUSTRIAL CONTROL TRANSFORMER</p> <p>250 VA 50/60Hz 80 °C RISE</p> <p>160 VA</p> <p>npl400c</p>	H1	H3	H2	H4	<p>LR3902 TYPE PH</p> <p>LISTED 252L E50394 130-9 TYPE 3AH</p>
	<p>240V HV</p> <p>1 3 2 4</p> <p>4 2 3 1</p> <p>12V LV</p>	<p>480V</p> <p>1 3 2 4</p> <p>4 2 3 1</p> <p>24V</p>	<p>CAT.NO. SP250QR</p> <p>H1 H3 H2 H4</p> <p>X4 X2 X3 X1</p>		

NOTES:



TITLE: SPARTAN 1 PHASE CONTROL TRANSFORMER

SHEET 1 OF 1

DBSP250QR

DES: WWONG
DATE: 09/10/19
SCALE: NTS
NO. DATE BY REVISION